PRODUCT SPEC SHEET ZEBRA DS4308-HC





THE DS4308-HC IDEAL FOR...

- Medication administration
- Blood product administration
- Specimen tracking
- Medication tracking in the pharmacy and on the pharmacy cart
- Electronic healthcare record access
- Patient identification

ZEBRA DS4308-HC

PROTECT PATIENT HEALTH WITH NEXT GENERATION BAR CODE SCANNING

IMPROVE PATIENT SAFETY AND INCREASE CAREGIVER PRODUCTIVITY WITH NEXT GENERATION SCANNING.

Bar code scanning at patient bedside is crucial in preventing medication and specimen mixups — two of the potentially deadliest errors in a hospital. But scanning bar codes in a hospital can be a challenge. There are many types of bar codes including traditional paper-based, those displayed on an electronic screen, codes printed on curved surfaces, high density codes printed On very small items and bar codes in all types of conditions — from smudged to scratched and poorly printed. Now, you can give your healthcare workers the ability to scan them all with the ds4308-hc. This feature-rich next generation 2d imager resets the bar for scanning performance, scanning range, versatility and ease-of-use. The result? The priceless peace of mind that the right patient received the right medication and the right test results, every time. The ds4308-hc — the ideal companion for laptops on workstation-on-wheels (wows) and other types of carts in your hospital.

PRZM Intelligent Imaging technology for next generation performance

Resets the bar for 2D imaging by improving decode performance and snappiness, ensuring the virtually instant capture of bar codes required in the mission critical world of healthcare.

Megapixel sensor and advanced algorithms enable first time capture of any bar code, on any medium — in virtually any condition

Give your healthcare workers true peace of mind with the ability to scan virtually any 1D, 2D or PDF417 bar code, as well as the many challenging bar codes in healthcare — including the tiny dense codes wrapped around the curved surface of a vial to bar codes that are stained or smudged.

Largest "sweet spot" for can't-miss point-and-shoot scanning simplicity

A decode range allows healthcare workers to scan any bar code type at any density nearer and farther than any other scanners in its class, making scanning truly second nature. And with omni-directional scanning, healthcare workers never need to waste valuable time aligning bar code and scanner.

Withstands constant disinfecting

IP42 sealing and a specially designed disinfectant-ready plastic housing allow safe wipe-down with a wide variety of harsh chemicals to help prevent the spread of germs.

Unsurpassed aiming technology

The crisp and bright aiming dot has the reach and brightness needed to ensure the fast capture of data.

Durable design for superior uptime

Built to survive a 6 ft./1.83 m drop to concrete, the DS4308-HC delivers reliable operation, despite the inevitable everyday drops.

COMPLIMENTARY MANAGEMENT TOOLS

Simplify and reduce the cost of everyday management with our nocost tools. 123Scan2 and Scanner Management Service (SMS) work hand-in-hand to reduce management time and cost by automating initial configuration and enabling remote management of your DS4308-HC scanners.

Day and night 'do-not-disturb' modes

Healthcare workers can choose to mix and match the decode feedback that is right for the moment: visual (green light/red light), haptic (vibration) and an audible tone.

Superior out-of-box experience

The DS4308-HC is up and running almost instantly. Smart auto-host detect cables automatically determine which interface is attached, eliminating the need to scan numerous configuration bar codes. Over 90 international keyboards are hosted within the scanner for easy setup, all around the world.

Easy on the eyes

Pitch

± 65° or greater

Thanks to a special LED wavelength and recessed lighting, when a bar code is scanned, the light that is emitted is soft and unobtrusive, preventing eye fatigue and improving the environment for patients and healthcare workers.

GIVE YOUR HEALTHCARE WORKERS THE POWER TO CAPTURE ANY BAR CODE, ON ANY MEDIUM, IN ANY CONDITION — AND MAKE YOUR HOSPITAL A SAFER PLACE.

For more information, visit www.zebra.com/ds4308hc or access our global contact directory at www.zebra.com/contact

PHYSICAL CHA	ARACTERISTICS	SYMBOLOGY DECODE CAPABILITY		
Dimensions	6.48 in. H x 3.86 in. L x 2.64 in. W 16.5 cm H x 9.8 cm L x 6.7 cm W	1-D	UPC/EAN, UPC/EAN with supplementals,	
Weight (w/o cable)	5.71 oz. / 162 g	-	Bookland EAN, ISS N, UCC Coupon	
Power	5 VDC ± 10% @ 360 mA (RMS typical)	-	Extended Code, Code 128, GS1- 128, ISB T 128, Code 39, Code 39 Full ASCII.	
Interfaces Supported	USB , RS232, Keyboard Wedge, RS485 (IBM 46xx) , SS I The scanner supports the following protocols over USB : HID Keyboard (default mode), SNAPI, IBM SurePOS (Yellowstone) (IBM Handheld, IBM Tabletop, OPOS), USB CDC, SS I over USB CDC, Toshiba TEC The scanner supports the following protocols over RS232: Standard, Wincor Nixdorf, ICL, Fujitsu, Olivetti, Omron and CUTE		Trioptic Code 39, Code 32, Code 93, Code 11, Matrix 2 of 5, Interleaved 2 of 5, Discrete 2 of 5, Codabar, MS I, Chinese 2 of 5, GS1 DataBar variants, Korean 3 of 5, ISB T Concat	
		2-D	PDF417, MicroPDF417, Composite Codes, TLC-39, Data Matrix, Maxicode, QR Code, MicroQR, Aztec, Han Xin	
		Postal	Australian Post, US PLANET, Royal Mail 4 State Customer, US POS TNET, KIX Code	
PERFORMANCE CHARACTERISTICS			(Dutch), UK Postal, Japan Post, UPU 4	
Light Source	Aiming pattern: 617 nm LED Illumination: 660 nm LEDs	-	State Postal FICS (Post US4), USPS 4 State	
Imager Field of View	ager Field of View 36° (H) x 22.5° (V)		Postal (Post US3), Canadian Post (Postbar)	
Roll	0 - 360°	Minimum Resolution	SR: Code 39 4 mil. UPC 60% 7.8	

mil.

Yaw	± 60° or greater	PDF417 5 mil, Datamatrix 7.5 mil
Print Contrast	20% minimum reflective difference	HD: Code 39 3 mil, UPC 60% 7.8 mil,
Motion Tolerances	Up to 30 in. / 76.2 cm per second	PDF417 4 mil, Datamatrix 5 mil

Motion Tolerances	op to 30 in. / /6.2 cm per second	13. The finite parameter of the		
ACCESSORIES		USER ENVIRONMENT		
Hands-Free Options	Gooseneck Intellistand	Operating Temp.	32° F to 122° F/0° C to 50° C	
Power Supplies	Power supplies are available for applications that do not supply power over the host cable	Storage Temp.	-40° F to 158° F/-40° C to 70° C	
		Humidity	5% to 95%, non-condensing	
		Drop Specification	Withstands multiple 6 ft./1.83 m drops to concrete	
WARRANTY		Ambient Light	Immune to normal indoor lighting	
Subject to the terms of Zebra's hardware warranty statement, the DS4308-HC is warranted against defects in workmanship and materials for a period of 5 years from the date of shipment. For the complete Zebra hardware product warranty statement, go to: http://www.zebra.com/warranty		- Immunity	up to 1600 Lux; immune to sunlight up to 86,000 Lux	
		REGULATORY		
		Electrical Safety	UL60950-1 2nd ed, CSA C22.2 No . 60950-1 2nd ed, EN60950-1/IEC60950-1 2nd ed.	
			IEC 62471:2006 and EN 62471: 2008	
			FCC Part 15 Class B, ICES-003 Class B, EN55022 Class B, EN55024, Medical Electrical Equipment: EN60601-1-2	
		Environmental	Compliant with RoHS directive 2011/65/EU	
		RECOMMENDED SERVICES		
		Enjoy easy access to fast repair and expert support with Service from the Start; add "next business day" replacement with Advanced Exchange.		

DECODE RANGES

HD FOCUS RANGE		TYPICAL WORKING RANGE	
BAR CODE TYPE	SYMBOL DENSITY	NEAR	FAR
Code 128	3.0 mil	1.0 in / 2.5 cm	3.0 in / 7.6 cm
Code 39	3.0 mil	0.5 in / 1.3 cm	5.8 in / 14.6 cm
Code 39	5.0 mil	0.0 in / 0.0 cm	10.0 in / 25.4 cm
micro PDF	4 mil	1.0 in /2.5 cm	4.7 in / 11.9 cm
PDF417	6.6 mil	0.2 in / 0.5 cm	7.8 in / 19.7 cm

UPC	13 mil	0 in / 0 cm	16.5 in / 41.9 cm
Datamatrix	5 mil	1.2 in / 3.0 cm	3.5 in / 8.9 cm
Datamatrix	7.5 mil	1.0 in / 2.5 cm	6.5 in / 16.5 cm
Datamatrix	10.0 mil	0.8 in / 1.9 cm	8.2 in / 20.8 cm
Code 39	20.0 mil	0 in / 0 cm	30.0 in / 76.2 cm
QR	10.0 mil	0 in / 0 cm	7.0 in / 17.8 cm
QR	20.0 mil	0.5 in / 1.3 cm	11.0 in / 27.9 cm

123Scan² Programs scanner parameters, upgrades firmware, provides scanned bar code data and prints reports.

www.zebra.com/123scan2

Scanner Management Service (SMS) Remotely manages your

Zebra scanner and queries its asset information.

Part number: SS -DS4308HC. Printed in USA 04/15.©2015 ZIH Corp, ZEBRA, the Zebra head graphic and Zebra Technologies logo are trademarks of ZIH Corp,

www.zebra.com/sms

registered in many jurisdictions worldwide. All rights reserved. All other trademarks are the property of their respective owners.

Scanner SDk

Generates a fully-featured scanner application, including documentation, drivers, test utilities and sample source code.

www.zebra.com/software



ZEBRA TECHNOLOGIES